

795+T5



Sicherheitsschrank Hoch 2 Türen Typ 90 - EN 14470-1 - 5 Schubladen

ÜBEREINSTIMMUNG


EN 14470-1, FM 6050

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

SONDERN AUCH...

- Adjustable shelves in height
- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Fixation for earthing
- 90-minute fire resistant according to EN 14470-1, and tested until 105 minute
- Tested and approved according to FM 6050
- Tested and approved with ISO 834 fire heating curve by an European laboratory



TECHNISCHE DATEN

Referenz
Übereinstimmung
Baustoffe der Sicherheitsschränke

795+T5
EN 14470-1, FM 6050
Stahl 12/10

Türfarbe
Anzahl der Türen
Art der Türen
Scharniere

weiß RAL 9010
2
flügeltüren
rechts und links

Verriegelung der Türen
Versandabmessungen HxBxT (mm)
Belüftung

Durchmesser der Öffnungen (mm)
Anzahl der Abteile / Fächer
Auffangwanne
Codenummer

selbstschließend
2150 x 1200 x 800
zuluftöffnung und abluftöffnung
auf dem dach
100
1
1
94032080

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Lüftungskasten (Réf : CDV-A)
- Filteraufsätze (ohne Filter) - NF X 15-211 (Réf : H50C)
- Anschlüsse für Filteraufsätze (Réf : KRC)

Referenz	Außere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Lagerkapazität (L)	Auffangwanne	Regale	Tragfähigkeit	Gewicht (Kg)
795+T5	1950 x 1137 x 620	1620 x 1000 x 410	250	1	0	50	495.00