

795+T6



# Sicherheitsschrank Hoch 2 Türen Typ 90 - EN 14470-1 - 6 Schubladen

## ÜBEREINSTIMMUNG

EN 14470-1, FM 6050

## ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

## SONDERN AUCH...

- Adjustable shelves in height
- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Fixation for earthing
- 90-minute fire resistant according to EN 14470-1, and tested until 105 minute
- Tested and approved according to FM 6050
- Tested and approved with ISO 834 fire heating curve by an European laboratory



## TECHNISCHE DATEN

|                                   |                            |                                |                                                     |
|-----------------------------------|----------------------------|--------------------------------|-----------------------------------------------------|
| Referenz                          | <b>795+T6</b>              | Verriegelung der Türen         | <b>selbstschließend</b>                             |
| Übereinstimmung                   | <b>EN 14470-1, FM 6050</b> | Versandabmessungen HxBxT (mm)  | <b>2150 x 1200 x 800</b>                            |
| Baustoffe der Sicherheitsschränke | <b>Stahl 12/10</b>         | Belüftung                      | <b>zuluftöffnung und abluftöffnung auf dem dach</b> |
| Türfarbe                          | <b>weiß RAL 9010</b>       | Durchmesser der Öffnungen (mm) | <b>100</b>                                          |
| Anzahl der Türen                  | <b>2</b>                   | Anzahl der Abteile / Fächer    | <b>1</b>                                            |
| Art der Türen                     | <b>flügeltüren</b>         | Auffangwanne                   | <b>1</b>                                            |
| Scharniere                        | <b>rechts und links</b>    | Codenummer                     | <b>94032080</b>                                     |

## COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Lüftungskasten (Réf : CDV-A)
- Filteraufsätze (ohne Filter) - NF X 15-211 (Réf : H50C)
- Anschlüsse für Filteraufsätze (Réf : KRC)

| Referenz | Außere Abmessungen HxBxT (mm) | Innere Abmessungen HxBxT (mm) | Lagerkapazität (L) | Auffangwanne | Regale | Tragfähigkeit | Gewicht (Kg) |
|----------|-------------------------------|-------------------------------|--------------------|--------------|--------|---------------|--------------|
| 795+T6   | 1950 x 1137 x 620             | 1620 x 1000 x 410             | 250                | 1            | 0      | 50            | 507.00       |