

Elektronische Codesperre

ÜBEREINSTIMMUNG

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

SONDERN AUCH...

- 4-digit code
- 2-point fixing
- Operates on 2 AA batteries (included), up to 80.000 cycles per pair of batteries
- Battery level indicator
- Several operating modes (private or public)
- LED indicator light



TECHNISCHE DATEN

Referenz

SERCODE

Referenz	Äußere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Lagerkapazität (L)	Auffangwanne	Regale	Tragfähigkeit	Gewicht (Kg)
SERCODE			0		0	0	0.00