

Class II Microbiological safety cabinet, 1200 mm wide

ÜBEREINSTIMMUNG

EN 12469

ADVANTAGES

- Convenient for micro-organisms

SONDERN AUCH...

- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged



TECHNISCHE DATEN

Referenz	PSM12	Elektrische Spannung (volts)	220
Übereinstimmung	EN 12469	Elektrische Spannung (Volt)	0.99999
Versandabmessungen HxBxT (mm)	1540 x 1450 x 850	Anschlusswert (W)	1860
Einströmgeschwindigkeit (m/s)	0,4	Codenummer	84146011

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for PSM12 (Réf : FACPSM12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Referenz	Äußere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Gewicht (Kg)
PSM12	1400 x 1360 x 795	650 x 1190 x 600	220.00