

# Manual pump intended to measure an activated carbon filter saturation

## ÜBEREINSTIMMUNG

---

## ADVANTAGES

---

- Convenient for the measure of the filter's saturation
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics



## TECHNISCHE DATEN

---

Referenz	<b>PMAF</b>	Codenummer	<b>90271000</b>
Referenz	Äußere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Gewicht (Kg)
PMAF			2.00