

Vertical laminar air flow cabinet, 900 wide

ÜBEREINSTIMMUNG

EN 61010-1, EN 61326-1, EN 61000-6-3

ADVANTAGES

SONDERN AUCH...

- Low noise fan
- High intensity of light
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- White walls for a glare-free brightness
- Easy replacement of the filters
- Electronic compartment located outside the contaminated area
- Microprocessor control system with digital display for airflow velocity
- Audible and visual alarm in case of airflow defect



TECHNISCHE DATEN

Referenz	FLV09	Durchflussstrom (m3/h)	2150
Übereinstimmung	EN 61010-1, EN 61326-1, EN 61000-6-3	Elektrische Spannung (Volt)	0.99999
Versandabmessungen HxBxT (mm)	1500 x 1150 x 850	Anschlusswert (W)	760
Einströmgeschwindigkeit (m/s)	0,4	Codenummer	84146011
Elektrische Spannung (volts)	220		

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for FLV09 (Réf : FACFLV09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Referenz	Äußere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Gewicht (Kg)
FLV09	1345 x 1060 x 795	620 x 890 x 630	165.00