

Vertical laminar air flow cabinet, 1200 wide


ÜBEREINSTIMMUNG

EN 61010-1, EN 61326-1, EN 61000-6-3

ADVANTAGES

SONDERN AUCH...

- Audible and visual alarm in case of airflow defect
- Electronic compartment located outside the contaminated area
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Microprocessor control system with digital display for airflow velocity
- Low noise fan



TECHNISCHE DATEN

Referenz	FLV12	Durchflussstrom (m3/h)	2150
Übereinstimmung	EN 61010-1, EN 61326-1, EN 61000-6-3	Zeitähler	Inclus
Versandabmessungen HxBxT (mm)	1500 x 1450 x 850	Elektrische Spannung (Volt)	0.99999
Einströmgeschwindigkeit (m/s)	0.4	Anschlusswert (W)	760
Elektrische Spannung (volts)	220	Codenummer	84146011

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for FLV12 (Réf : FACFLV12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Referenz	Äußere Abmessungen HxBxT (mm)	Innere Abmessungen HxBxT (mm)	Gewicht (Kg)
FLV12	1345 x 1360x 795	620 x 1195 x 630	185.00