

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Dedicated hole for cable through
- Proven resistance of 105 minutes



TECHNICAL FEATURES

Model	793+NLI	Shipping dimensions HxWxD (mm)	1300 x 1200 x 800
Body color	black	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	black	Openings diameter (mm)	100
Number of doors	2	Connecting sleeve	1
Hinges	left and right	Number of compartments	1
Door closure	automatic closing	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Perforated shelf for 2-door safety cabinet (Réf : E35LI)
- 79°C Special Lithium Battery Automatic Fire Extinguisher (Réf : EX100LI)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Visual & audible alarm + control box + smoke detector + fire extinguisher EX100LI + cable duct (Réf : VIG190)
- Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
793+NLI	1100 x 1137 x 670	820 x 1000 x 410	0		0	0	297.00