

High security cabinet 90 min lithium batteries 2 doors + 1 fire extinguisher EX200LI + 4 shelves E35LI

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Proven resistance of 105 minutes
- Reduce the risk of fire and explosion



TECHNICAL FEATURES

Model	795+LIA4	Shipping dimensions HxWxD (mm)	2150 x 1200 x 800
Cabinet materials	Sheet steel 12/10th and inner body built in melami white RAL 9010	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Connecting sleeve	1
Doors type	swing doors	Number of compartments	1
Hinges	left and right	HS Code	94032080
Door closure	automatic closing		

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated shelf for 2-door safety cabinet (Réf : E35LI)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Rack of 9 electrical outlets (Réf : PRISELI)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)
- Filtration box with activated carbon filter for organic and corrosive vapors (Réf : CDF-ACORG)
- Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Visual & audible alarm + control box + smoke detector + fire extinguisher EX200Li + cable duct (Réf : VIG290)
- Connecting kit (Réf : KRC)
- Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
795+LIA4	1950 x 1137 x 620	1620 x 1000 x 410	0		4	100	483.00