

793+LIX2



Low Safety cabinet 90 min for lithium batteries 2 doors + VIG190 + 2 E35LI

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Reduce the risk of fire and explosion
- Proven resistance of 105 minutes



TECHNICAL FEATURES

Model	793+LIX2	Openings diameter (mm)	100
Number of doors	2	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Retention shelf for 2-door safety cabinets Types 30, 60 & 90 (Réf : E35)
- Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Connecting kit (Réf : KRC)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
793+LIX2	1100 x 1137 x 670	820 x 1000 x 410	0		2	80	302.00