

795+LIX4



Safety cabinet 90 min for lithium batteries High 2 doors + VIG290 + 4 E35LI

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Reduce the risk of fire and explosion
- 105-minute fire resistant and made in France



TECHNICAL FEATURES

Model	795+LIX4	Shipping dimensions HxWxD (mm)	2150 x 1200 x 800
Doors color	white RAL 9010	Ventilation	Both inlet and outlet on the top of the cabinet
Number of doors	2	Openings diameter (mm)	100
Doors type	swing doors	Connecting sleeve	1
Hinges	left and right	Number of compartments	1
Door closure	automatic closing	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)
- Perforated shelf for 2-door safety cabinet (Réf : E35LI)
- Rack of 9 electrical outlets (Réf : PRISELI)
- Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
795+LIX4	1950 x 1137 x 620	1620 x 1000 x 410	0		4	100	488.00