

793+LI



Security cabinet 90 min lithium batteries – Counter cabinet 2 doors to equip

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Proven resistance of 105 minutes
- Reduce the risk of fire and explosion



TECHNICAL FEATURES

Model	793+LI	Shipping dimensions HxWxD (mm)	1300 x 1200 x 800
Cabinet materials	Sheet steel 12/10th and inner body built in melami	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Connecting sleeve	1
Doors type	swing doors	Number of compartments	1
Hinges	left and right	HS Code	94032080
Door closure	automatic closing		

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

• Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)	• Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)	• Filtration box with activated carbon filter for organic and corrosive vapors (Réf : CDF-ACORG)	• Ventilation box for a connection to the outside (Réf : CDV-A)	• Recirculating air box Labopur - NF X 15-211 (Réf : H50C)	• Connecting kit (Réf : KRC)
• Perforated shelf for 2-door safety cabinet (Réf : E35LI)	• 79°C Special Lithium Battery Automatic Fire Extinguisher (Réf : EX100LI)	• Rack of 9 electrical outlets (Réf : PRISELI)	• Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)	• Visual & audible alarm + control box + smoke detector + fire extinguisher EX100Li + cable duct (Réf : VIG190)	• Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)
• Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)	• Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)				

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
793+LI	1100 x 1137 x 670	820 x 1000 x 410	0		0	0	297.00