

795+BE



2- door tall safety cabinet Type 90 – for maritime motion

COMPLIANCE

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- EN 14470-1 and FM 6050 compliant
- Storage of flammables

BUT ALSO...

- Adjustable shelves in height
- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Fixation for earthing
- 90-minute fire resistant according to EN 14470-1, and tested until 105 minute
- Tested and approved by a independent European laboratory
- 3 ground fastenings by screwing
- Non-slipping mat allowing to absorb leakage and avoid possible sliding of recipients during maritime motion
- Wall fixation kit to prevent maritime motion



TECHNICAL FEATURES

Model	795+BE	Ventilation	Both inlet and outlet on the top of the cabinet
Compliance	EN 14470-1, EN 1363-1	Openings diameter (mm)	100
Cabinet materials	12/10th epoxy painted steel structure	Connecting sleeve	1
Doors color	white RAL 9010	Number of compartments	1
Number of doors	2	Shelves in PVC	Option
Doors type	swing doors	Containment sump	1
Hinges	left and right	Containment sump in PVC	Option
Door closure	automatic closing	Grating	Option
Shipping dimensions HxWxD (mm)	2150 x 1200 x 800	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 2- door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Retention shelf for 2-door safety cabinets Types 30, 60 & 90 (Réf : E35)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 2-door safety cabinets Types 30, 60 & 90 (Réf : T235)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
795+BE	1950 x 1137 x 620	1620 x 1000 x 410	250	1	3	50	453.00



138 avenue Henri BARBUSSE 92140 Clamart (France)
Tél. 01 46 45 80 00 - Fax : 01 46 45 85 98
www.trionyx.fr - trionyx[at]trionyx.fr