

Security cabinet – Tall cabinet 2 doors to equip

COMPLIANCE

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- Storage of lithium-ion batteries

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Proven resistance of 105 minutes
- Reduce the risk of fire and explosion



TECHNICAL FEATURES

Model	795+LI	Shipping dimensions HxWxD (mm)	2150 x 1200 x 800
Cabinet materials	Sheet steel 12/10th and inner body built in melami	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Connecting sleeve	1
Doors type	swing doors	Number of compartments	1
Hinges	left and right	HS Code	94032080
Door closure	automatic closing		

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)
- Filtration box with activated carbon filter for organic and corrosive vapors (Réf : CDF-ACORG)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Visual & audible alarm + control box + smoke detector + fire extinguisher EX200Li + cable duct (Réf : VIG290)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- 79°C Special Lithium Battery Automatic Fire Extinguisher for 795+LI cabinet (Réf : EX200LI)
- Connecting kit (Réf : KRC)
- Rack of 9 electric outlets type F (Germany) (Réf : PRISELIF)
- Rack of 9 electrical outlets (Réf : PRISELI)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
795+LI	1950 x 1137 x 620	1620 x 1000 x 410	0		0	80	453.00