

3035UE



## 2- door tall safety cabinet Type 30

### COMPLIANCE

EN 14470-1, FM 6050

### ADVANTAGES

- 30-minute fire resistant and made in France
- EN 14470-1 and FM 6050 compliant
- Storage of flammables

•

### BUT ALSO...

- Thermo-expanding seals of the doors
- Adjustable leveling feet for enhance stability
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Pedestal area under-driveable by a forklift by removing panel
- Tested and approved according to FM 6050



### TECHNICAL FEATURES

|                   |                                |                                |                                                              |
|-------------------|--------------------------------|--------------------------------|--------------------------------------------------------------|
| Model             | <b>3035UE</b>                  | Door closure                   | <b>self-closing</b>                                          |
| Compliance        | <b>EN 14470-1, FM 6050</b>     | Shipping dimensions HxWxD (mm) | <b>1950 x 1200 x 800</b>                                     |
| Cabinet materials | <b>Melamine wood structure</b> | Ventilation                    | <b>Both inlet and outlet on the back wall of the cabinet</b> |
| Doors color       | <b>light grey RAL 7035</b>     | Openings diameter (mm)         | <b>100</b>                                                   |
| Number of doors   | <b>2</b>                       | Number of compartments         | <b>1</b>                                                     |
| Doors type        | <b>swing doors</b>             | Containment sump               | <b>1</b>                                                     |
| Hinges            | <b>right &amp; left</b>        | HS Code                        | <b>94036000</b>                                              |

### ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

### OPTIONS

- Containment sump for cabinets 3033UE - 3035UE (Réf : B35U)
- Retention shelf for cabinets 3033UE - 3035UE (Réf : E35U)

| Model  | External dimensions HxWxD (mm) | Internal dimensions HxWxD (mm) | Storage capacity (L) | Containment sump | Shelves | Load capacity | Weight (kg) |
|--------|--------------------------------|--------------------------------|----------------------|------------------|---------|---------------|-------------|
| 3035UE | 1731 x 1092 x 457              | 1330 x 978 x 325               | 170                  | 1                | 2       | 50            | 210.00      |