

3035E



2 doors safety cabinet Type 30

COMPLIANCE

EN 14470-1, FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- EN 14470-1 and FM 6050 compliant
- Storage of flammables

BUT ALSO...

- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Adjustable leveling feet for enhance stability
- Pedestal area under-driveable by a forklift by removing panel
- Tested and approved according to FM 6050



TECHNICAL FEATURES

Model	3035E	Shipping dimensions HxWxD (mm)	2200 x 1200 x 800
Compliance	EN 14470-1, FM 6050	Ventilation	Both inlet and outlet on the back wall of the cabinet
Cabinet materials	Melamine wood structure	Openings diameter (mm)	100
Doors color	light grey RAL 7035	Number of compartments	1
Number of doors	2	Containment sump	1
Doors type	swing doors	Containment sump in PVC	option
Hinges	right & left	Grating	option
Door closure	self-closing	HS Code	94036000

ADDITIONAL ACCESSORIES RECOMMENDED - FILTRATION OR VENTILATION BOXES

- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 2-door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Retention shelf for 2-door safety cabinets Types 30, 60 & 90 (Réf : E35)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 2-door safety cabinets Types 30, 60 & 90 (Réf : T235)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
3035E	1980 x 1115 x 550	1580 x 1050 x 420	250	1	3	50	210.00