

3035M31



2- door tall safety cabinet Type 30 - 4 compartments

COMPLIANCE

EN 14470-1, FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- EN 14470-1 and FM 6050 compliant
- Storage of flammables, corrosives and toxics

BUT ALSO...

- Thermo-expanding seals of the doors
- Adjustable leveling feet for enhance stability
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Compartments allowing the separation of different types of chemicals
- Tested and approved according to FM 6050



TECHNICAL FEATURES

Model	3035M31	Door closure	self-closing
Compliance	EN 14470-1, FM 6050	Shipping dimensions HxWxD (mm)	2180 x 1200 x 800
Cabinet materials	Melamine wood structure	Ventilation	Both inlet and outlet on the back wall of the cabinet
Doors color	light grey RAL 7035	Openings diameter (mm)	100
Number of doors	2	Number of compartments	4
Doors type	swing doors	Containment sump	4
Hinges	right & left	HS Code	94036000

ADDITIONAL ACCESSORIES RECOMMENDED - FILTRATION OR VENTILATION BOXES

- Filtration box with activated carbon filter for organic vapors (Réf : CDF-A)
- Filtration box with activated carbon filter for organic and corrosive vapors (Réf : CDF-ACORG)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 1- door cabinets Types 30, 60 & 90 (Réf : B148)
- Perforated cover plate for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : C148)
- Retention shelf for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : E48)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : T148)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
3035M31	1980 x 1115 x 550	(1581 x 491 x 419) + (3 x 514) x 491 x 419	1	4	6	30	244.00