

2- door tall safety cabinet Type 60

COMPLIANCE

EN 14470-1, EN 1363-1

ADVANTAGES

- 60-minute fire resistant and made in France
- EN 14470-1 and EN 1363-1 compliant
- Storage of flammables

BUT ALSO...

- Thermo-expanding seals of the doors
- EN 14470-1 Type 60 compliant
- Adjustable shelves in height
- Locking system
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Fixation for earthing
- Tested and approved with ISO 834 fire heating curve by an European laboratory



TECHNICAL FEATURES

Model	765+	Door closure	self-closing
Compliance	EN 14470-1, EN 1363-1	Shipping dimensions HxWxD (mm)	2080 x 1200 x 800
Cabinet materials	12/10th epoxy painted steel structure	Ventilation	Both inlet and outlet on the back wall of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Number of compartments	1
Doors type	swing doors	HS Code	94032080
Hinges	right & left		

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Filtration box with activated carbon filter for organic vapors (Réf : cdfa)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 2- door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Retention shelf for 2-door safety cabinets Types 30, 60 & 90 (Réf : E35)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 2-door safety cabinets Types 30, 60 & 90 (Réf : T235)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
765+	1950 x 1137 x 620	1620 x 1000 x 410	250		0	0	435.00