

795+T4



## 2- door tall safety cabinet Type 90 with 4 sliding drawers

### COMPLIANCE

EN 14470-1

### ADVANTAGES

- 105-minute fire resistant and made in France
- EN 14470-1 and EN 1363-1 compliant
- Storage of flammables

### BUT ALSO...

- Adjustable shelves in height
- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Fixation for earthing
- 90-minute fire resistant according to EN 14470-1, and tested until 105 minute
- Tested and approved according to FM 6050
- Tested and approved with ISO 834 fire heating curve by an European laboratory



### TECHNICAL FEATURES

Model	<b>795+T4</b>	Door closure	<b>self-closing</b>
Compliance	<b>EN 14470-1</b>	Shipping dimensions HxWxD (mm)	<b>2150 x 1200 x 800</b>
Cabinet materials	<b>12/10th epoxy painted steel structure</b>	Ventilation	<b>Both inlet and outlet on the top of the cabinet</b>
Doors color	<b>white RAL 9010</b>	Openings diameter (mm)	<b>100</b>
Number of doors	<b>2</b>	Number of compartments	<b>1</b>
Doors type	<b>swing doors</b>	Containment sump	<b>4</b>
Hinges	<b>right &amp; left</b>	HS Code	<b>94032080</b>

### ADDITIONAL ACCESSORIES RECOMMENDED - FILTRATION OR VENTILATION BOXES

- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
795+T4	1950 x 1137 x 620	1620 x 1000 x 410	250	4	0	50	483.00