

2- door working cover safety cabinet Type 90

COMPLIANCE

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables
- EN 14470-1 and FM 6050 compliant

.

BUT ALSO...

- Adjustable shelves in height
- Locking system
- Adjustable shelves in height
- Holes for the connection to the ventilation
- Thermo-expanding seals of the doors
- Fixation for earthing
- Normalized labelling provided with the equipment
- Fixation for earthing
- 90-minute fire resistant according to EN 14470-1, and tested until 105 minute
- Tested and approved by a independent European laboratory
- Tested and approved according to FM 6050
- Normalized labelling provided with the equipment



TECHNICAL FEATURES

Model	793+E	Door closure	self-closing
Compliance	EN 14470-1, EN 1363-1	Shipping dimensions HxWxD (mm)	1300 x 1200 x 800
Cabinet materials	12/10th epoxy painted steel structure	Ventilation	Both inlet and outlet on the back wall of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Number of compartments	1
Doors type	swing doors	Containment sump	1
Hinges	right & left	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED - FILTRATION OR VENTILATION BOXES

- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NFX 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 2- door cabinets Types 30, 60 & 90 (Réf : B235)
- Perforated cover plate for 2-door safety cabinets Types 30, 60 & 90 (Réf : C235)
- Retention shelf for 2-door safety cabinets Types 30, 60 & 90 (Réf : E35)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 2-door safety cabinets Types 30, 60 & 90 (Réf : T235)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
793+E	1100 x 1137 x 670	820 x 1000 x 410	115	1	2	50	297.00