


790+2FLI35



Storage and utility cupboard – 105 mm – tall, 2 doors – XXL – P3500T1

COMPLIANCE

ADVANTAGES

- Connected alarm | smoke detector
- Fire extinguisher
- Manual security check
- French manufacturing - CSR
- The most powerful battery can reach up to 3500 Wh
- Open-door alarm
- Flame protection system
- Dry contact
- Tested 105 min - from outside to inside in accordance with standard EN14470-1
- Circuit breaker
- Ballistic protection system
- Storage of lithium-ion batteries
- Inside to outside fire-stop construction EI180

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Reduce the risk of fire and explosion



TECHNICAL FEATURES

Model	790+2FLI35	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Connecting sleeve	1
Doors type	swing doors	Number of compartments	1
Hinges	left and right	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Breakthrough for cable entry with fire-resistant cable (Réf : PEXTBALI)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Rack of 8 electric outlets type F (Germany) (Réf : PRISELIF)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
790+2FLI35	2102 x 1502 x 903	1685 x 1350 x 695	0		4	0	702.00



138 avenue Henri BARBUSSE 92140 Clamart (France)
Tél. 01 46 45 80 00 - Fax : 01 46 45 85 98
www.trionyx.fr - trionyx[at]trionyx.fr