


G804+LI10



Storage and display cabinet – counter, 2-door – P1000T1

COMPLIANCE

ADVANTAGES

- Connected alarm | smoke detector
- Open-door alarm
- Circuit breaker
- Fire extinguisher
- Flame protection system
- Ballistic protection system
- Manual security check
- Dry contact
- Storage of lithium-ion batteries
- French manufacturing - CSR

BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Reduce the risk of fire and explosion

TECHNICAL FEATURES

Model	G804+LI10	Ventilation	Both inlet and outlet on the top of the cabinet
Cabinet materials	12/12 double-walled steel	Openings diameter (mm)	100
Doors color	white RAL 9010	Connecting sleeve	1
Number of doors	2	Number of compartments	1
Doors type	swing doors	HS Code	94032080
Hinges	left and right		

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Rack of 9 electrical outlets (Réf : PRISELI)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Rack of 8 electric outlets type F (Germany) (Réf : PRISELIF)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
G804+LI10	935 x 1000 x 450	745 x 950 x 400	0		2	0	77.00