


G806+LI10



# Storage and display cabinet – counter, 2-door – P1000T1

## COMPLIANCE

## ADVANTAGES

- Connected alarm | smoke detector
- Open-door alarm
- Circuit breaker
- Fire extinguisher
- Flame protection system
- Ballistic protection system
- Manual security check
- Dry contact
- Storage of lithium-ion batteries
- French manufacturing - CSR

## BUT ALSO...

- Locking system
- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Reduce the risk of fire and explosion

## TECHNICAL FEATURES

Model	<b>G806+LI10</b>	Ventilation	<b>Both inlet and outlet on the top of the cabinet</b>
Cabinet materials	<b>12/12 double-walled steel</b>	Openings diameter (mm)	<b>100</b>
Doors color	<b>white RAL 9010</b>	Connecting sleeve	<b>1</b>
Number of doors	<b>2</b>	Number of compartments	<b>1</b>
Doors type	<b>swing doors</b>	HS Code	<b>94032080</b>
Hinges	<b>left and right</b>		

## ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Rack of 9 electrical outlets (Réf : PRISELI)
- Rack of 6 electrical outlets equipped with a thermal-magnetic circuit breaker (Réf : PRISELICC)
- Rack of 7 G-type electrical outlets (UK) (Réf : PRISELIUK)
- Rack of 8 electrical outlets type J (Switzerland) (Réf : PRISELICH)
- Rack of 8 electric outlets type F (Germany) (Réf : PRISELIF)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
G806+LI10	935 x 1000 x 600	745 x 950 x 550	0		2	0	92.00