

Class II Microbiological safety cabinet, 900 mm wide

COMPLIANCE


EN 12469

ADVANTAGES

- Convenient for micro-organisms

BUT ALSO...

- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged



TECHNICAL FEATURES

Model	PSM9	Voltage (volts)	0.99999
Compliance	EN 12469	Electrical power (W)	1860
Airflow (m/s)	0,4	HS Code	84146011
Voltage (volts)	220		

COMPLEMENTARY PRODUCTS

- Front enclosure with UV light for PSM9 (Réf : FACPSM09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
PSM9	1390 x 1050 x 790	630 x 885 x 630	144.00