

FLV09

EN
61010-1EN
61326-1EN
61000-6-3

Vertical laminar air flow cabinet, 900 wide

COMPLIANCE

EN 61010-1, EN 61326-1, EN 61000-6-3

ADVANTAGES

• • •

BUT ALSO...

- Low noise fan
- High intensity of light
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- White walls for a glare-free brightness
- Easy replacement of the filters
- Electronic compartment located outside the contaminated area
- Microprocessor control system with digital display for airflow velocity
- Audible and visual alarm in case of airflow defect



TECHNICAL FEATURES

Model	FLV09	Flow (m3/h)	2150
Compliance	EN 61010-1, EN 61326-1, EN 61000-6-3	Voltage (volts)	0.99999
Shipping dimensions HxWxD (mm)	1500 x 1150 x 850	Electrical power (W)	760
Airflow (m/s)	0,4	HS Code	84146011
Voltage (volts)	220		

COMPLEMENTARY PRODUCTS

- Front enclosure with UV light for FLV09 (Réf : FACFLV09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
FLV09	1345 x 1060 x 795	620 x 890 x 630	165.00