

# Ductless fume hood 900 mm - 2 Modules - for liquid & powder - one opening

## COMPLIANCE

NF X 15-211 Classe 1

## ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

- Draft standard EN 17242

## BUT ALSO...

- Easy replacement of the active coal filter
- Low acoustic level
- Front control window to see immediately the filter
- NF X 15-211 compliant
- Delivered ready to use
- Lighting control allowing to survey the proper working of the fan
- Glass side walls
- Ergonomic hand traps or trapezoidal opening



## TECHNICAL FEATURES

Model	<b>H092Z+H2C</b>	Hour counter	<b>included</b>
Compliance	<b>NF X 15-211 Classe 1</b>	Sampling outlet	<b>included</b>
Airflow (m/s)	<b>0,4 - 0,6</b>	Backwall transparent	<b>included</b>
Voltage (volts)	<b>220-240</b>	Melamine work-top	<b>option</b>
Flow (m <sup>3</sup> /h)	<b>170</b>	Electrical power (W)	<b>27</b>
Openings for passages of cables	<b>4</b>	Sound power of the fan dB(A)	<b>57,00</b>
Anemometer	<b>included</b>	HS Code	<b>84146000</b>
Guide of chemicals adsorbed	<b>included</b>		

## COMPLEMENTARY PRODUCTS

- Activated carbon filter for ammonia vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Activated carbon filter for organic and corrosive vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Activated carbon filter for formaldehyde vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- HEPA filter for ductless fume hoods H201 - H211 (Réf : HEP200)
- Activated carbon filter for organic vapors for H200 - H201 - H210 - H211 (Réf : ORG200)
- HEPA filter frame for H201 - H211 (Réf : SH200)
- Containment sump and melamine work-top for H09 (Réf : BB09)
- Containment sump and tempered glass work-top for H09 (Réf : BV09)

## OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H09 (Réf : TA09)
- Trolley with adjustable shelf for H09 (Réf : TR09)
- Tubular table with feet for model H09 (Réf : TTF09)
- Tubular table with wheels for model H09 (Réf : TTR09)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
H092Z+H2C	1160 x 900 x 750	935 x 845 x 700	34.00