

H152Z+



Ductless fume hood 1500 mm - 2 Modules - one opening

COMPLIANCE

NF X 15-211 Classe 2

ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

BUT ALSO...

- Low acoustic level
- Front control window to see immediately the filter
- Easy replacement of the active coal filter
- NF X 15-211 compliant
- Delivered ready to use
- Holes for the cables and fluid going through
- Glass side walls
- Ergonomic hand traps or trapezoidal opening
- Lighting control allowing to survey the proper working of the fan



TECHNICAL FEATURES

Model	H152Z+	Hour counter	included
Compliance	NF X 15-211 Classe 2	Sampling outlet	included
Airflow (m/s)	0,5	Backwall transparent	included
Voltage (volts)	220-240	Melamine work-top	option
Flow (m ³ /h)	170	Electrical power (W)	27
Openings for passages of cables	4	Sound power of the fan dB(A)	57.00
Anemometer	included	HS Code	84146000
Guide of chemicals adsorbed	included		

COMPLEMENTARY PRODUCTS

- Activated carbon filter for ammonia vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- HEPA filter frame for H201 - H211 (Réf : SH200)
- Kit to use the fume hood without activated carbon filter - for old fume hoods type 200, 201, 210 and 211 (Réf : CAR200)
- HEPA filter frame for H201 - H211 (Réf : SH200)
- Activated carbon filter for organic and corrosive vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Containment sump and melamine work-top for H15 (Réf : BB15)
- Activated carbon filter for formaldehyde vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Containment sump and tempered glass work-top for H15 (Réf : BV15)
- HEPA filter for ductless fume hoods H201 - H211 (Réf : HEP200)
- Activated carbon filter for organic vapors for H200 - H201 - H210 - H211 (Réf : ORG200)

OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H15 (Réf : TA15)
- Trolley with adjustable shelf for H15 (Réf : TR15)
- Tubular table with feet for model H15 (Réf : TTF15)
- Tubular table with wheels for model H15 (Réf : TTR15)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
H152Z+	1160 x 1500 x 750	935 x 1445 x 700	54.00