

H092D+



Ductless fume hood 900 mm - 2 Modules - two openings

COMPLIANCE

NF X 15-211 Classe 2

ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

- Draft standard EN 17242

BUT ALSO...

- Low acoustic level
- Front control window to see immediately the filter
- Easy replacement of the active coal filter
- NF X 15-211 compliant
- Delivered ready to use
- Holes for the cables and fluid going through
- Glass side walls
- Ergonomic hand traps or trapezoidal opening
- Lighting control allowing to survey the proper working of the fan



TECHNICAL FEATURES

Model
Compliance
Airflow (m/s)
Voltage (volts)
Flow (m3/h)
Openings for passages of cables
Anemometer
Guide of chemicals adsorbed

H092D+
NF X 15-211 Classe 2
0,5
220-240
170
4
included
included

Hour counter
Sampling outlet
Backwall transparent
Melamine work-top
Electrical power (W)
Sound power of the fan dB(A)
HS Code

included
included
included
option
27
57.00
84146000

COMPLEMENTARY PRODUCTS

- Activated carbon filter for ammonia vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Kit to use the fume hood without activated carbon filter - for old fume hoods type 200, 201, 210 and 211 (Réf : CAR200)
- Activated carbon filter for organic and corrosive vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Activated carbon filter for formaldehyde vapors - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- HEPA filter for ductless fume hoods H201 - H211 (Réf : HEP200)
- Activated carbon filter for organic vapors for H200 - H201 - H210 - H211 (Réf : ORG200)
- HEPA filter frame for H201 - H211 (Réf : SH200)
- Containment sump and melamine work-top for H09 (Réf : BB09)
- Containment sump and tempered glass work-top for H09 (Réf : BV09)

OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H09 (Réf : TA09)
- Trolley with adjustable shelf for H09 (Réf : TR09)
- Tubular table with feet for model H09 (Réf : TTF09)
- Tubular table with wheels for model H09 (Réf : TTR09)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
H092D+	1160 x 900 x 750	935 x 845 x 700	34.00