

Ventilation box with ATEX engine – filtration in option

COMPLIANCE

ATEX Zone 2

ADVANTAGES

- CE certified
- ATEX zone II certified
- ATEX certified

BUT ALSO...

- Suitable on any safety cabinet
- ATEX certified
- Simple and aesthetic fitting
- Lighting control allowing to survey the proper working of the fan
- Easy and aesthetic installation
- Allow the extraction of the chemicals vapors contained in the cabinet



TECHNICAL FEATURES

Model
Compliance

CMAT
ATEX Zone 2

Shipping dimensions HxWxD (mm)
HS Code

700 x 500 x 500
84145940

COMPLEMENTARY PRODUCTS

- Activated carbon filter for organic and corrosive vapors - for filtration box type CDF or cabinet AF10 (Réf : CDFCORG)
- Activated carbon filter for formaldehyde vapors - for filtration box type CDF or cabinet AF10 (Réf : CDFFOR)
- Activated carbon filter for organic vapors - for filtration box type CDF or cabinet AF10 (Réf : CDFORG)
- Clamp collar - diameter 100 mm (Réf : CDS100)
- Connection sleeve - diameter 100 mm (Réf : CHJ)
- Flexible sleeve in PVC - 1 meter (Réf : KL100)
- Connecting kit (Réf : KRC)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Weight (kg)
CMAT	305 x 650 x 285		18.00