

S806T



2- door working cover safety cabinet

COMPLIANCE

NF EN ISO 1182

ADVANTAGES

- 2- point locking system
- NF EN ISO 1182 compliant
- Storage of flammables and toxics

BUT ALSO...

- Containment sump at the bottom
- 2- point locking system
- Self-closing doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Non-flammable insulation between the walls



TECHNICAL FEATURES

Model	S806T	Door closure	automatic closing
Compliance	NF EN ISO 1182	Shipping dimensions HxWxD (mm)	1100 x 1200 x 800
Cabinet materials	12/10th epoxy painted steel structure	Ventilation	Both inlet and outlet
Doors color	white RAL 9010	Openings diameter (mm)	100
Number of doors	2	Number of compartments	1
Doors type	swing doors	Containment sump	1
Hinges	right & left	HS Code	94032080

ADDITIONAL ACCESSORIES RECOMMENDED – FILTRATION OR VENTILATION BOXES

- Filtration box with activated carbon filter for organic vapors (Réf : cdfa)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump in PVC (Réf : BP06)
- Shelf protection in PVC (Réf : EP06)
- Additional retention shelf (Réf : G06)
- Additional containment sump (Réf : GL06)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
S806T	895 x 1000 x 600	745 x 950 x 550	135	1	1	75	90.00