

S804T



## 2- door working cover safety cabinet

### COMPLIANCE

NF EN ISO 1182

### ADVANTAGES

- 2- point locking system
- NF EN ISO 1182 compliant
- Storage of flammables and toxics

### BUT ALSO...

- Containment sump at the bottom
- 2- point locking system
- Self-closing doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Non-flammable insulation between the walls



### TECHNICAL FEATURES

Model	<b>S804T</b>	Containment sump	<b>1</b>
Compliance	<b>NF EN ISO 1182</b>	Airflow (m/s)	<b>0,5</b>
Cabinet materials	<b>12/10th epoxy painted steel structure</b>	Voltage (volts)	<b>220-240</b>
Doors color	<b>white RAL 9010</b>	Flow (m3/h)	<b>170</b>
Number of doors	<b>2</b>	Anemometer	<b>Oui</b>
Doors type	<b>Type de porte(s)</b>	Guide of chemicals adsorbed	<b>Oui</b>
Hinges	<b>right &amp; left</b>	Hour counter	<b>Oui</b>
Door closure	<b>manual closing</b>	Sampling outlet	<b>Oui</b>
Ventilation	<b>Both inlet and outlet</b>	Backwall transparent	<b>Non</b>
Openings diameter (mm)	<b>100</b>	HS Code	<b>94032080</b>
Number of compartments	<b>1</b>		

### ADDITIONAL ACCESSORIES RECOMMENDED - FILTRATION OR VENTILATION BOXES

- Filtration box with activated carbon filter for organic vapors (Réf : cdfa)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recirculating air box Labopur - NF X 15-211 (Réf : H50C)
- Connecting kit (Réf : KRC)

### OPTIONS

- Containment sump in PVC (Réf : BP04)
- Shelf protection in PVC (Réf : EP04)
- Additional retention shelf (Réf : G04)
- Additional containment sump (Réf : GL04)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
S804T	895 x 1000 x 450	745 x 950 x 400	100	1	1	75	75.00