

## Safety eye-washer - wall mounted for indoor use

### COMPLIANCE

EN 15154-2

### ADVANTAGES

- ISO 3864 compliant
- EN 15154-2 compliant
- First-aid in case of chemical projection

### BUT ALSO...

- Anti-dust caps for dusty environment
- Compliant to the article R. 4224-14 of the Labour Code
- Allows to rinse itself the eyes in case of chemical projection
- Delivered with the first-aid labelling
- EN 15154-2 compliant



### TECHNICAL FEATURES

|                                |                         |              |  |
|--------------------------------|-------------------------|--------------|--|
| Model                          | <b>LV13</b>             | Bowl         | <b>Green ABS RAL 6029</b>                              |
| Compliance                     | <b>EN 15154-2</b>       | Pipe         | <b>galvanised steel + green epoxy painted RAL 6029</b> |
| Shipping dimensions HxWxD (mm) | <b>320 x 320 x 220</b>  | Water inlet  | <b>F 1 / 2"</b>  |
| Use                            | <b>internal use</b>     | Water outlet | <b>F1 1 / 4"</b>                                       |
| Setting                        | <b>handle operating</b> | HS Code      | <b>73242921</b>  |
|                                | <b>wall mounted</b>     |              |  |

### OPTIONS

- Thermostatic mixing valve for safety eye-wash (Réf : MCL)

| Model | External dimensions HxWxD (mm) | Internal dimensions HxWxD (mm) | Eye-washer flow (L/min) | Shower flow (L/min) | Weight (kg) |
|-------|--------------------------------|--------------------------------|-------------------------|---------------------|-------------|
| LV13  |                                |                                | 11                      | 0                   | 5.00        |