

## Safety eye-washer - wall mounted for indoor use

### COMPLIANCE

EN 15154-2

### ADVANTAGES

- ISO 3864 compliant
- EN 15154-2 compliant
- First-aid in case of chemical projection

### BUT ALSO...

- Anti-dust caps for dusty environment
- Compliant to the article R. 4224-14 of the Labour Code
- Allows to rinse itself the eyes in case of chemical projection
- Delivered with the first-aid labelling
- EN 15154-2 compliant



### TECHNICAL FEATURES

Model	<b>LV23</b>	Bowl	<b>Green ABS RAL 6029</b>
Compliance	<b>EN 15154-2</b>	Pipe	<b>galvanised steel + green epoxy painted RAL 6029</b>
Shipping dimensions HxWxD (mm)	<b>340 x 220 x 800</b>	Water inlet	<b>F 1 / 2"</b>
Use	<b>internal use</b>	Water outlet	<b>F1 1 / 4"</b>
Setting	<b>handle operating</b>	HS Code	<b>73242921</b>
	<b>mounted on feet</b>		

### OPTIONS

- Thermostatic mixing valve for safety eye-wash (Réf : MCL)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Eye-washer flow (L/min)	Shower flow (L/min)	Weight (kg)
LV23	H1050		11	0	10.00