

B45S



# Armadio di sicurezza FM per prodotti corrosivi - 170 L - Automatico

## CONFORMIDAD

FM - OSHA - NFPA

## ADVANTAGES

- NFPA and OSHA compliant
- Conforme a la norma FM
- Storage of corrosives

## SINO TAMBIÉN...

- Containment sump integrated with HDPE protection
- NFPA, OSHA and FM compliant
- Rugged construction with double wall
- Adjustable shelves in height with HDPE protection
- Integrated door handle
- Self-closing doors



## CARACTERISTICAS TECNICAS

Modelo	<b>B45S</b>	Cierre de las puertas	<b>chiusura automatica</b>
Conformidad	<b>FM - OSHA - NFPA</b>	Dimensiones de envío alt x anc x pro (mm)	<b>1850 x 1200 x 800</b>
Materiales del armario	<b>acciaio doppia parete</b>	Ventilación	<b>orificio di ventilazione alto e bassi, con griglia</b>
Color de las puertas	<b>blu</b>	Diámetro de ventilación (mm)	<b>50</b>
Número de puertas	<b>2</b>	Número de compartimentos	<b>1</b>
Tipo de puertas	<b>porte battenti</b>	Código Aduanero	<b>2147483647</b>
Bisagras	<b>cerniere a destra e sinistra</b>		

## COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di filtrazione acciaio Filtra CORG (Réf : CDF-ACORG)
- Cassettone di filtrazione PVC cellulare (Réf : )
- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Gerla ed armadi hanno filtrazione - Ventilazione - Cassettone ha recirculation di aria senza filtro (Réf : H50C)
- Kit di raccordo per cassettone (Réf : KRC)

## OPTIONS

- Mensola supplementare per armadio 170 L (Réf : ESP45)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
B45S	1651 x 1092 x 457	1560 x 1005 x 390	170		2	159	123.00