

MR9+



Armadio multirischi 90 min - EN 14470-1 - PVC cellulare

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Built in cellular PVC for acids-bases-toxics compartments
- Holes for the connection to the ventilation
- Fixation for earthing (for flammable part)
- Self-closing door if the temperature rises to 47°C



CARACTERISTICAS TECNICAS

Modelo	MR9+	Cierre de las puertas	chiusura automatica e manuale
Conformidad	EN 14470-1, EN 1363-1	Dimensiones de envío alt x anc x pro (mm)	2400 x 1300 x 800
Materiales del armario	melamina e acciaio 15/10 doppia parete	Ventilación	entrata dell'aria laterale e uscita sul tetto
Color de las puertas	bianco RAL 9010	Diámetro de ventilación (mm)	100
Número de puertas	4	Número de compartimentos	4
Tipo de puertas	porte battenti	Cubetas de retención	1
Bisagras	cerniere a destra e sinistra	Código Aduanero	94032080

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di filtrazione PVC cellulare (Réf :)
- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Gerla ed armadi hanno filtrazione - Ventilazione - Cassettone ha recirculation di aria senza filtro (Réf : H50C)
- Kit di raccordo per cassettoni (Réf : KRC)

OPTIONS

- Etagere/bac di ritenzione supplementare per gli scompartimenti acidi, basi, tossici (Réf : E8A2)
- Carabottino per tragheto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Cassetto/tragheto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Carabottino per tragheto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Cassetto/tragheto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Cassetto/tragheto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
MR9+	2205 x 1270 x 615		210	1	3	30	400.00