

795+M13



Armadio multirischi 105 minuti - 4 scompartimenti

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Tested and approved according to FM 6050
- Compartments allowing the separation of different types of chemicals



CARACTERISTICAS TECNICAS

Modelo	795+M13	Cierre de las puertas	chiusura automatica
Conformidad	EN 14470-1, EN 1363-1	Dimensiones de envío alt x anc x pro (mm)	2150 x 1200 x 800
Materiales del armario	acciaio 12/10 e pareti interne in melamina	Ventilación	Prese di entrata e di uscita dell'aria sul tetto
Color de las puertas	bianco RAL 9010	Diámetro de ventilación (mm)	100
Número de puertas	2	Número de compartimentos	4
Tipo de puertas	porte battenti	Cubetas de retención	4
Bisagras	cerniere a destra e sinistra	Código Aduanero	94032080

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Kit di raccordo per cassettone (Réf : KRC)

OPTIONS

- traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Traghetto di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Traghetto di ritenzione in PVC (Réf : SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
795+M13	1950 x 1137 x 620	1620 x 490 x 410 + (3 x 533) x 490 x 410	204	4	6	30	489.00