

795+M13



Armadio multirischi 105 minuti - 4 scompartimenti

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Tested and approved according to FM 6050
- Compartments allowing the separation of different types of chemicals



CARACTERISTICAS TECNICAS

| | | | |
|------------------------|---|---|---|
| Modelo | 795+M13 | Cierre de las puertas | chiusura automatica |
| Conformidad | EN 14470-1, EN 1363-1 | Dimensiones de envío alt x anc x pro (mm) | 2150 x 1200 x 800 |
| Materiales del armario | acciaio 12/10 e pareti interne in melamina | Ventilación | Prese di entrata e di uscita dell'aria sul tetto |
| Color de las puertas | bianco RAL 9010 | Diámetro de ventilación (mm) | 100 |
| Número de puertas | 2 | Número de compartimentos | 4 |
| Tipo de puertas | porte battenti | Cubetas de retención | 4 |
| Bisagras | cerniere a destra e sinistra | Código Aduanero | 94032080 |

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Gerla ed armadi hanno filtrazione - Ventilazione - Cassettone ha recirculation di aria senza filtro (Réf : H50C)
- Kit di raccordo per cassettone (Réf : KRC)

OPTIONS

- traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Traghetto di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Traghetto di ritenzione in PVC (Réf : SB148)

| Modelo | Dimensiones exteriores alt x anc x pro (mm) | Dimensiones interiores alt x anc x pro (mm) | Capacidad de almacenamiento (L) | Cubetas de retención | Estanterías | Carga admisible | Peso (kg) |
|---------|---|---|---------------------------------|----------------------|-------------|-----------------|-----------|
| 795+M13 | 1950 x 1137 x 620 | 1620 x 490 x 410 + (3 x 533) x 490 x 410 | 204 | 4 | 6 | 30 | 489.00 |