

795+M22



Armadio multirischi 105 minuti - 4 scompartimenti

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Tested and approved according to FM 6050
- Compartments allowing the separation of different types of chemicals



CARACTERISTICAS TECNICAS

Modelo	795+M22	Dimensiones de envío alt x anc x pro (mm)	2150 x 1200 x 800
Conformidad	EN 14470-1, EN 1363-1	Ventilación	Prese di entrata e di uscita dell'aria sul tetto
Materiales del armario	acciaio 12/10 e pareti interne in melamina	Diámetro de ventilación (mm)	100
Color de las puertas	bianco RAL 9010	Número de compartimentos	4
Número de puertas	2	Cubetas de retención	4
Tipo de puertas	porte battenti	Rejilla	4
Bisagras	cerniere a destra e sinistra	Código Aduanero	94032080
Cierre de las puertas	chiusura automatica		

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Kit di raccordo per cassettoni (Réf : KRC)

OPTIONS

- Traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Traghetto di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
795+M22	1950 x 1137 x 620	4x (800x490x410)	220	4	4	30	497.00