

3035M11



Armadio Multirischi 30 minuti - 2 scompartimenti

CONFORMIDAD

EN 14470-1, FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Compartments allowing the separation of different types of chemicals
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

Modelo	3035M11	Cierre de las puertas	chiusura automatica
Conformidad	EN 14470-1, FM 6050	Dimensiones de envío alt x anc x pro (mm)	2180 x 1200 x 800
Materiales del armario	melamina	Ventilación	Prese di entrata e di uscita dell'aria sul tetto
Color de las puertas	grigio chiaro RAL 7035	Diámetro de ventilación (mm)	100
Número de puertas	2	Número de compartimentos	2
Tipo de puertas	porte battenti	Cubetas de retención	2
Bisagras	cerniere a destra e sinistra	Código Aduanero	94036000

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di filtrazione acciaio Filtra ORG (Réf : CDF-A)
- Gerla ed armadi hanno filtrazione - Ventilazione - Cassettone ha recirculation di aria senza filtro (Réf : H50C)
- Kit di raccordo per cassettone (Réf : KRC)

OPTIONS

- tragheto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per tragheto di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Cassetto/tragheto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Tragheto di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Cassetto/tragheto scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Tragheto di ritenzione in PVC (Réf : SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
3035M11	1980 x 1115 x 550	1581 x (2 x 982) x 419	240	2	6	30	232.00