

3034M3



Armadio Multirischi 30 minuti - 3 scompartimenti

CONFORMIDAD

EN 14470-1, FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Compartments allowing the separation of different types of chemicals
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

Modelo	3034M3	Cierre de las puertas	chiusura automatica
Conformidad	EN 14470-1, FM 6050	Dimensiones de envío alt x anc x pro (mm)	2180 x 1200 x 800
Materiales del armario	melamina	Ventilación	Prese di entrata e di uscita dell'aria sul tetto
Color de las puertas	grigio chiaro RAL 7035	Diámetro de ventilación (mm)	100
Número de puertas	1	Número de compartimentos	3
Tipo de puertas	porte battenti	Cubetas de retención	3
Bisagras	cerniere a destra	Código Aduanero	94036000

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Kit di raccordo per cassettoni (Réf : KRC)

OPTIONS

- traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Traghettino di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE48)
- Cassetto/traghettino scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Carabottino per traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Cassetto/traghettino scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE48)
- Traghettino di ritenzione in PVC (Réf : SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
3034M3	1980 x 605 x 550	(3 x 514) x 491 x 419	90	3	3	30	129.00