

3035M22



Armadio Multirischi 30 minuti - 4 scompartimenti

CONFORMIDAD

EN 14470-1, FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Compartments allowing the separation of different types of chemicals
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

Modelo **3035M22**
 Conformidad **EN 14470-1, FM 6050**
 Materiales del armario **melamina**
 Color de las puertas **grigio chiaro RAL 7035**
 Número de puertas **2**
 Tipo de puertas **porte battenti**
 Bisagras **cerniere a destra e sinistra**

Cierre de las puertas
 Dimensiones de envío alt x anc x pro (mm)
 Ventilación

chiusura automatica
2180 x 1200 x 800

Diámetro de ventilación (mm)
 Número de compartimentos
 Cubetas de retención
 Código Aduanero

Prese di entrata e di uscita dell'aria sul tetto
100
4
4
94036000

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Kit di raccordo per cassettone (Réf : KRC)

OPTIONS

- traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : B148)
- Carabottino per traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Traghettino di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE48)
- Cassetto/traghettino scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Mensola di ritenzione supplementare per lo scompartimento infiammabile (Réf : E48)
- Carabottino per traghettino di ritenzione per armadio 1 porta - L 635 - P 615 mm (Réf : C148)
- Cassetto/traghettino scorrevole per armadio 1 porta - L 635 - P 615 mm (Réf : T148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE48)
- Traghettino di ritenzione in PVC (Réf : SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
3035M22	1980 x 1115 x 550	(2 x 781) x (2 x 982) x 419	220	4	8	30	252.00