

793+E



## armadio 105 minuti - 2 mensole - 1 traghetto

### CONFORMIDAD

EN 14470-1, EN 1363-1

### ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

### SINO TAMBIÉN...

- Adjustable shelves in height
- Adjustable shelves in height
- Holes for the connection to the ventilation
- Tested and approved by a independent European laboratory
- Tested and approved according to FM 6050



### CARACTERISTICAS TECNICAS

Modelo	<b>793+E</b>	Cierre de las puertas	<b>chiusura automatica</b>
Conformidad	<b>EN 14470-1, EN 1363-1</b>	Dimensiones de envío alt x anc x pro (mm)	<b>1300 x 1200 x 800</b>
Materiales del armario	<b>acciaio 12/10 e pareti interne in melamina</b>	Ventilación	<b>Prese di entrata e di uscita dell'aria dietro</b>
Color de las puertas	<b>bianco RAL 9010</b>	Diámetro de ventilación (mm)	<b>100</b>
Número de puertas	<b>2</b>	Número de compartimentos	<b>1</b>
Tipo de puertas	<b>porte battenti</b>	Cubetas de retención	<b>1</b>
Bisagras	<b>cerniere a destra e sinistra</b>	Código Aduanero	<b>94032080</b>

### COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Kit di raccordo per cassettone (Réf : KRC)

### OPTIONS

- traghetto di ritenzione per armadio 2 porte - L 1135 - P 615 mm (Réf : B235)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf : C235)
- Mensola di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf : E35)
- Traghetto di ritenzione in PVC (Réf : SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Cassetto/traghetto scorrevole per armadio 2 porte - L 1135 - P 615 mm (Réf : T235)
- Mensola di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf : E35)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf : C235)
- Cassetto/traghetto scorrevole per armadio 2 porte - L 1135 - P 615 mm (Réf : T235)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf : SE148)
- Traghetto di ritenzione in PVC (Réf : SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
793+E	1100 x 1137 x 670	820 x 1000 x 410	115	1	2	50	297.00