

armadio 105 minuti - 2 mensole - 1 traghetto (copie)

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

SINO TAMBIÉN...

- Adjustable shelves in height
- Adjustable shelves in height
- Holes for the connection to the ventilation
- Tested and approved by a independent European laboratory
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

Modelo	793+PJE	Cierre de las puertas	chiusura automatica
Conformidad	EN 14470-1, EN 1363-1	Dimensiones de envío alt x anc x pro (mm)	1300 x 1200 x 800
Materiales del armario	acciaio 12/10 e pareti interne in melamina	Ventilación	Prese di entrata e di uscita dell'aria dietro
Color de las puertas	bianco RAL 9010	Diámetro de ventilación (mm)	100
Número de puertas	2	Número de compartimentos	1
Tipo de puertas	porte battenti	Cubetas de retención	1
Bisagras	cerniere a destra e sinistra	Código Aduanero	94032080

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf: CDV-A)
- Kit di raccordo per cassettone (Réf: KRC)

OPTIONS

- traghetto di ritenzione per armadio 2 porte - L 1135 - P 615 mm (Réf: B235)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf: C235)
- Mensola di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf: E35)
- Traghetto di ritenzione in PVC (Réf: SB148)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf: SE48)
- Cassetto/traghetto scorrevole per armadio 2 porta - L 1135 - P 615 mm (Réf: T235)
- Mensola di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf: E35)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 1135 - P 615 mm (Réf: C235)
- Cassetto/traghetto scorrevole per armadio 2 porta - L 1135 - P 615 mm (Réf: T235)
- Su mensola di ritenzione in PVC per armadio ha 1 porta in L 615 mm - Per i modelli 2 porte in L 1135, prevedere 2 locali da livello (Réf: SE48)
- Traghetto di ritenzione in PVC (Réf: SB148)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
793+PJE	1100 x 1137 x 670	820 x 1000 x 410	115	1	2	50	297.00