

791T



armadio 105 minuti hanno cassetto

CONFORMIDAD


EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

| | | | |
|------------------------|---|---|--|
| Modelo | 791T | Dimensiones de envío alt x anc x pro (mm) | 900 x 1200 x 800 |
| Conformidad | EN 14470-1, EN 1363-1 | Ventilación | Prese di entrata e di uscita dell'aria dietro |
| Materiales del armario | acciaio 12/10 e pareti interne in melamina | Diámetro de ventilación (mm) | 100 |
| Color de las puertas | bianco RAL 9010 | Número de compartimentos | 1 |
| Número de puertas | 1 | Cubetas de retención | 1 |
| Tipo de puertas | porte scorrevoli | Código Aduanero | 94032080 |
| Cierre de las puertas | chiusura automatica | | |

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Kit di raccordo per cassettone (Réf : KRC)
- Vertical recycling air box (delivered without filter) (Réf : H40+)

OPTIONS

- Grigliati (Réf : C1T)

| Modelo | Dimensiones exteriores alt x anc x pro (mm) | Dimensiones interiores alt x anc x pro (mm) | Capacidad de almacenamiento (L) | Cubetas de retención | Estanterías | Carga admisible | Peso (kg) |
|--------|---|---|---------------------------------|----------------------|-------------|-----------------|-----------|
| 791T | 670 x 635 x 615 | 460 x 490 x 380 | 30 | 1 | 0 | 0 | 155.00 |