

795+900



armadio 105 minuti nuvola ha attrezzare

CONFORMIDAD

EN 14470-1, EN 1363-1

ADVANTAGES

- 105-minute fire resistant and made in France
- Storage of flammables

SINO TAMBIÉN...

- Holes for the connection to the ventilation
- Tested and approved according to FM 6050



CARACTERISTICAS TECNICAS

Modelo	795+900	Cierre de las puertas	chiusura automatica
Conformidad	EN 14470-1, EN 1363-1	Dimensiones de envío alt x anc x pro (mm)	2150 x 1200 x 800
Materiales del armario	acciaio 12/10 e pareti interne in melamina	Ventilación	Prese di entrata e di uscita dell'aria sul tetto
Color de las puertas	bianco RAL 9010	Diámetro de ventilación (mm)	100
Número de puertas	2	Número de compartimentos	1
Tipo de puertas	porte battenti	Código Aduanero	94032080
Bisagras	cerniere a destra e sinistra		

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Cassettone di ventilazione in acciaio (Réf : CDV-A)
- Gerla ed armadi hanno filtrazione - Ventilazione - Cassettone ha recirculation di aria senza filtro (Réf : H50C)
- Kit di raccordo per cassettoni (Réf : KRC)

OPTIONS

- traghetto di ritenzione per armadio 2 porte - L 900 - P 615 mm (Réf : B235-900)
- Carabottino per traghetto di ritenzione per armadio 1 porta - L 900 - P 615 mm (Réf : C235-900)
- Mensola di ritenzione per armadio 1 porta - L 900 - P 615 mm (Réf : E235-900)
- Cassetto/traghetto scorrevole per armadio 1 porta - L 900 - P 615 mm (Réf : T235-900)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
795+900	1950 x 905 x 620	1620 x 765 x 410	200		0	0	420.00