

ASC20

## Secured cabinet with 20 individual lockers

### CONFORMIDAD

Article L. 511-5

### ADVANTAGES

- Possibility to fix on the wall
- Individual key closing
- Individual label holder for each locker
- Individual reinforced door with noise damper



### CARACTERISTICAS TECNICAS

Modelo	<b>ASC20</b>	Tipo de puertas	<b>Swinging</b>
Conformidad	<b>Article L. 511-5</b>	Bisagras	<b>Right</b>
Materiales del armario	<b>High-strength steel and grey epoxy paint RAL 7035</b>	Cierre de las puertas	<b>Manual</b>
Color de las puertas	<b>Blue RAL 7035</b>	Número de compartimentos	<b>20</b>
Número de puertas	<b>20</b>		

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
ASC20	1100 x 800 x 150		0		0	0	27.00