

ASC35

Secured cabinet with 35 individual lockers

CONFORMIDAD

ADVANTAGES

- Possibility to fix on the wall
- Individual label holder for each locker
- Individual reinforced door with noise damper
- Individual key closing



CARACTERISTICAS TECNICAS

Modelo
Materiales del armario

ASC35
High-strength steel and grey epoxy
paint RAL 7035
Blue RAL 7035
35

Tipo de puertas
Bisagras

Swinging
Right

Color de las puertas
Número de puertas

Cierre de las puertas
Número de compartimentos

Manual
35

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
ASC35	1100 x 1380 x 150		0		0	0	43.00