

ASC35

Secured cabinet with 35 individual lockers

CONFORMIDAD

ADVANTAGES

- Possibility to fix on the wall
- Individual label holder for each locker
- Individual reinforced door with noise damper
- Individual key closing



CARACTERISTICAS TECNICAS

Modelo	ASC35	Tipo de puertas	Swinging
Materiales del armario	High-strength steel and grey epoxy paint RAL 7035	Bisagras	Right
Color de las puertas	Blue RAL 7035	Cierre de las puertas	Manual
Número de puertas	35	Número de compartimentos	35

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Capacidad de almacenamiento (L)	Cubetas de retención	Estanterías	Carga admisible	Peso (kg)
ASC35	1100 x 1380 x 150		0		0	0	43.00