

H092D+2C



Ductless fume hood 900 mm - 2 Modules - for liquid - two openings

CONFORMIDAD

NF X 15-211 Classe 1

ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

SINO TAMBIÉN...

- Low acoustic level
- NF X 15-211 compliant
- Delivered ready to use
- Glass side walls
- Ergonomic hand traps or trapezoidal opening



CARACTERISTICAS TECNICAS

| | | | |
|--------------------------------|-----------------------------|---------------------------------------|-----------------|
| Modelo | H092D+2C | Guía de productos químicos adsorbidos | included |
| Conformidad | NF X 15-211 Classe 1 | Contador horario | included |
| Velocidad del aire (m/s) | 220-240 | Toma de muestras | included |
| Tensión (voltios) | 170 | Pared posterior transparente | included |
| Caudal de aire (m3/h) | 4 | Plan de trabajo de melamina | option |
| Evacuación | 0,4 - 0,6 | Potencia eléctrica (vatios) | 27 |
| Aberturas para pasos de cables | included | Potencia acústica del ventilador | 57.00 |
| Anemómetro | included | Código Aduanero | 84146000 |

PRODUITS COMPLÉMENTAIRES

- Filtro ha carbone attivo per vapori ammoniaci per sorbonne tipo 200 (Réf : AMM200)
- Filtro ha carbone attivo polivalente - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Filtro ha carbone attivo per formolo - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Filtro ha carbone attivo per vapori organici - for old fume hoods type 200, 201, 210 and 211 (Réf : ORG200)
- Containment sump and melamine work-top for H09 (Réf : BB09)
- Containment sump and tempered glass work-top for H09 (Réf : BV09)

OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H09 (Réf : TA09)
- Trolley with adjustable shelf for H09 (Réf : TR09)
- Tubular table with feet for model H09 (Réf : TTF09)
- Tubular table with wheels for model H09 (Réf : TTR09)

| Modelo | Dimensiones exteriores alt x anc x pro (mm) | Dimensiones interiores alt x anc x pro (mm) | Peso (kg) |
|----------|---|---|-----------|
| H092D+2C | 1160 x 900 x 750 | 935 x 845 x 700 | 34.00 |