

Vertical laminar air flow cabinet, 1200 wide


CONFORMIDAD

EN 61010-1, EN 61326-1, EN 61000-6-3

ADVANTAGES

SINO TAMBIÉN...

- Audible and visual alarm in case of airflow defect
- White walls for a glare-free brightness
- Microprocessor control system with digital display for airflow velocity
- Electronic compartment located outside the contaminated area
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Low noise fan
- High intensity of light
- Easy replacement of the filters



CARACTERISTICAS TECNICAS

Modelo	FLV12	Caudal de aire (m ³ /h)	2150
Conformidad	EN 61010-1, EN 61326-1, EN 61000-6-3	Contador horario	Inclus
Dimensiones de envío alt x anc x pro (mm)	1500 x 1450 x 850	Tensión (voltios)	0.99999
Velocidad del aire (m/s)	0,4	Potencia eléctrica (vatios)	760
Tensión (voltios)	220	Código Aduanero	84146011

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for FLV12 (Réf : FACFLV12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
FLV12	1345 x 1360x 795	620 x 1195 x 630	185.00